


Testen Sie  
unseren neuen  
**Entgratfräser**  
**Noventa**

---





<b>P1-3</b>	<b>M1,2</b>	VHM MD/SC	AlTiCrN+S	
<b>K1,2</b>	<b>N1-8</b>	Z 4		
<b>S1,2</b>	<b>O1</b>			
<b>H1,2</b>				

d <sub>1</sub>	d <sub>2</sub>	l <sub>2</sub>	l <sub>1</sub>	d <sub>3</sub>
mm	mm	mm	mm	mm
0.80	0.30	3.60	60	4.00
1.00	0.40	4.00	60	4.00
1.50	0.60	6.00	60	4.00
2.00	1.00	8.00	60	4.00
2.50	1.30	10.00	70	6.00
3.00	1.80	12.00	70	6.00
4.00	2.50	16.00	70	6.00
5.00	3.20	20.00	80	8.00
6.00	4.00	24.00	80	8.00